



PHARMAPEX[®]
Providing Healthcare Products Worldwide



Best Vision[™]
Soft Cosmetic Contact Lens
—————
— — — — —

BEST VISION™ CATALOGUE

A. Soft Lenses

These myopia-correcting soft lenses prevent cornea irritation and give comfort from the moment you first wear them!

The FDA-approved pigment and the high quality production practices guarantee eye health and safety. Using revolutionary production technologies, the surface of these lenses are smooth and the pigment does not wash off. In addition, they can be worn so gently that the wearer feels very comfortable, all while protecting eyes by reducing movement and securing clear sight.



B.C: 8.6
DIA: 14.0
COLOR: Blue (Tinted)
POWER: $\pm 0.00 \sim 10.00$ (0.25 step)

B. Astigmatism Lenses

Astigmatic-correcting lenses are very effective in correcting visual acuity all while being very comfortable. A soft and smooth connection on the surface of lenses gives comfort to wearers, and a customized design provides a sense of convenience. In addition, safe materials and high oxygen permeability cause little irritation on the cornea. The lenses are even comfortable when wearing for a long period of time. You can also enjoy a brighter view because there is no chromatic aberration.




B.C: 8.6
DIA: 14.0
COLOR: Blue (Tinted)
POWER: $\pm 0.00 \sim 10.00$ (0.25 step)

C. Circle Lenses

Made with new materials of minimized impurities, Best Vision™ Circle Lenses are of high refractive index and are very resilient. The lenses come in a variety of beautiful colors and do a great job of making your eyes pop. Safety of materials is guaranteed by FDA approval, and the pigment is absorbed in the materials so it does not leak out.




B.C: 8.6
DIA: 14.0
COLOR: Blue (Tinted)
POWER: $\pm 0.00 \sim 10.00$ (0.25 step)



BVDM21 - Brown




BVDM21 - Gray



BVDM23 - Brown



BVDM23 - Gray



BVDM26 - Gray




BVDM27 - Brown



BVDM30 - Brown



BVDM30 - Gray




BVDM11 - Brown




BVDM11 - Gray

D. 2 Color Lenses


These cosmetic lenses make your pupils look large and beautiful. There are a variety of colors to choose from, all of which emphasize cornea size in the color of your choice.




BV008 - Violet



BV008 - Aqua



BV008 - Brown




BV008 - Gray




BVA11 - Brown




BVA11 - Gray




BVA12 - Aqua



BVA12 - Brown




BVA12 - Gray




BVA12 - Green



BVA12 - Violet



BVA21 - Blue



BVA21 - Brown



BVA21 - Gray




BVA21 - Violet




BVAM02 - Brown



BVAM02 - Gray



BVAM77 - Aqua



BVAM77 - Brown



BVAM77 - Gray



BVAM77 - Violet



BVBT - Aqua



BVBT - Brown



BVBT - Gray



BVBT - Green



BVBT - Sky



BVBT - Violet



BVCL21 - Brown



BVCL21 - Gray



BVCL21 - Green



BVCL21 - Sky



BVCL21 - Violet



BVDB21 - Aqua



BVDB21 - Brown



BVDB21 - Gray




BVDB21 - Green



BVDB21 - Violet



BVDM21 - Brown




BVDM21 - Gray



BVDM21 - Green



BVDM21 - Violet



BVDM21 - Aqua



BVDM21 - Sky



BVDM23 - Brown



BVDM23 - Gray



BVDM24 - Aqua



BVDM24 - Brown



BVDM24 - Gray



BVDM24 - Hazel



BVDM24 - Violet



BVDM25 - Brown



BVDM25 - Gray




BVDM25 - Green



BVDM25 - Sky



BVDM25 - Violet




BVGB4 - Brown




BVH60 - Brown



BVH60 - Gray




BVH60 - Green




BVH60 - Sky




BVH60 - Violet




BVH70 - Aqua




BVH70 - Brown



BVH70 - Gray



BVH70 - Violet



BVHB - Aqua



BVHB - Brown



BVHB - Gray



BVHB - Green



BVHB - Violet




BVI.FAX - Brown




BVI.FAX - Gray



BVJ10 - Gray



BVM11 - Aqua




BVM11 - Brown



BVM11- Gray




BVM11- Green



BVM11 - Sky



BVM11 - Violet



BVMG - Brown




BVI.FAX - Brown




BVI.FAX - Gray



BVJ10 - Gray



BVM11 - Aqua




BVM11 - Brown



BVM11 - Gray




BVM11 - Green



BVM11 - Sky



BVM11 - Violet




BVMG - Brown




BVQ18 - Gray




BVQ18 - Violet




BVSS12 - Brown



BVSS12 - Gray



BVSS12 - Sky




BVSS12 - Violet



BVT173 - Brown



BVT173 - Gray



BVT174 - Brown



BVV10 - Brown



BVV10 - Gray




BVV10 - Sky



BVV10 - Violet




BVX4 - Brown




BVX4 - Gray




BVX4 - Hazel




BVX7 - Sky




BVY2 - Aqua




BVY2 - Brown




BVY2 - Gray




BVY2 - Green




BVY2 - Sky




BVY2 - Violet




BVY10 - Brown



BVY10 - Gray



BVY10 - Green



BVY10 - Sky



BVY10 - Violet



BVY50 - Gray



BVZ12 - Brown



BVZ12 - Gray



BVZ12 - Sky



BVZ12 - Violet



BVZ13 - Aqua



BVZ13 - Brown




BVZ13 - Gray




BVZ13 - Green



BVZ13 - Violet




BVD30 - Aqua




BVD30 - Brown




BVAD5 - Brown




BVAD5 - Blue




BVGB1 - 2Ton(Gray)




BVGB1 - 2Ton(Brown)



BVGB1 - 2Ton(Aqua)




BVJA1 - 2Ton(Gray)




BVJA1 - 2Ton(Green)



BVJA1 - 2Ton (Violet)



BVJA1 - 2Ton(Brown)



BVJA1 - 2Ton(Aqua)




BVMD - 2Ton(Gray)



BVMD - 2Ton(Green)



BVMD - 2Ton (Violet)




BVMD - 2Ton(Brown)




BVMD - 2Ton(Aqua)


E. 3 Color Lenses



BVCC1 - Aqua




BVCC1 - Gray



BVCC1 - Green



BVCC1 - Violet



BVCC1 - Brown



F. Type

Cosmetic three color lenses have been made with lathe cutting, resulting in natural and beautiful eyes. There are six types of colors to choose from, all made comfortable due to a high water content and stable refractive index.


A TYPE

WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)


B.C: **8.6**
DIA: **14.0, 14.5**


TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**

A TYPE — 1 COLOR




A TYPE — 2 COLOR





A TYPE — 3 COLOR





B TYPE

WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)



B.C: **8.6**
DIA: **14.5**

TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**

B TYPE — 2 COLOR



B TYPE — 3 COLOR





C TYPE

WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)

B.C: **8.6**
DIA: **14.5**

TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**

C TYPE — 3 COLOR




D TYPE

WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)


B.C: **8.6**
DIA: **14.0**

TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**


D TYPE — 1 COLOR



D TYPE — 2 COLOR



D TYPE — 3 COLOR




E TYPE

WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)

B.C: **8.6**
DIA: **14.0**


TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**

E TYPE — 2 COLOR





E TYPE — 3 COLOR




F TYPE

WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)


B.C: **8.6**
DIA: **14.0**

TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**

F TYPE — 2 COLOR



F TYPE — 3 COLOR




MO TYPE

WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)


B.C: **8.6**
DIA: **14.5**

TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**

MO TYPE — 2 COLOR



MO TYPE — 3 COLOR




MS TYPE

WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)

B.C: **8.6**
DIA: **14.5**

TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**

MS TYPE — 3 COLOR




S TYPE

WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)

B.C: **8.6**
DIA: **14.5**

TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**

S TYPE — 2 COLOR



SB TYPE

WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)

B.C: **8.6**
DIA: **14.5**

TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**

SB TYPE — 3 COLOR




SP TYPE

WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)


B.C: **8.6**
DIA: **14.5**

TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**

SP TYPE — 2 COLOR



SP TYPE — 3 COLOR




T TYPE

WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)

B.C: **8.6**
DIA: **14.5**

TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**

T TYPE — 3 COLOR



U TYPE


WATER CONTENT: **38%, 42%**
POWER RANGE & STEP: **S-0.00 ~ 6.00 (0.25 step)**
S-6.00 ~ 10.00 (0.50 step)

B.C: **8.6**
DIA: **14.5**




TECHNOLOGY: **Lathe Cutting**
PACKING: **Vial, Blister**

U TYPE — 3 COLOR





G. Crazy Lenses





BV 021



BV022



BV023



BV024



BV025



BV 026



BV027



BV028



BV 029



BV030



BV 031



BV032



BV 033



BV034



BV 035



BV 036



BV037



BV 038



BV040



BV 042



BV043



BV044



BV 045



BV046



BV 047



BV 048



BV 049



BV 050



BV 051



BV 052



BV 063



BV 064



BV 065



BV 066



BV 067



BV 068



BV 069



BV 070



BV 071



BV 072



BV 073



BV 074



BV 075



BV 076



BV 077



BV 078



BV 079



BV 082



BV 083



BV 084



BV085



BV086



BV087



BV088



BV089



BV090



BV091



BV092



BV093



BV094



BV095



BV096



BV097



BV098



BV099



BV100



BV101



BV102



BV103



BV104



BV105



BV106



BV107



BV108



BV109



BV110



BV111



BV112



BV113